

j4gPGEgaWQ9ImN0bDA1X01haW5OYXYxX2N0bDAyX3JwdENvbW1lcmNpYWxfY3RsMDNfcnB0Q29tbWVyY2lhbFN1Ym1lbnVfY3RsMDBfaGxDb21tZXJjaV



designed to be better.

Search

Communication Device

26TELTVICC10

Combination f type coaxial connector and four conductor RJ11 telephone jack. With one-piece molded plate decorator outline. Ivory.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

features & benefits

- Decorator outline.
- Face constructed of high-impact thermoplastic.
- Zinc-plated steel strap.
- Nickel-plated F-type connector.
- Threaded on each end.

specifications

General Info

- Color: Ivory
- Type: Communication Combination

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121704
- U R: No

Dimensions

- Depth (U S): 1.2
- Volume: 13.2
- Weight: 0.064
- Width U S: 2
- Height: 5.5

Technical Information

- Material: Steel

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No