



designed to be better.

[Search](#)

Medium Base Lampholder

280WH

Medium base, phenolic, pullchain, 4 terminals with tri-drive screws, fits 3 1/4 and 4" boxes, with cage necks. White.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- SPECIFICATIONS

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: Yes

- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 4.5"
- Height Metric: 2.00"

Technical Information

- Volts: 250V
- Volts A C: 250
- Watts: 250

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: Trade Agreement Act Compliant
-