

N0ZWQtb3V0bGV0cy5hc3B4ZBYCZg8WAh8ABYQBPGItZyByZXBsYWNIPSJkc3JjIiBkc3JjPSlVfi9tZWRpYS8xQzQzODdDQUNGODI0MEYwOTUwMjE4REQ:



designed to be better.

Search

Medium Base Lampholder

282

Medium base, porcelain, pullchain, 2 terminals with tri-drive screws fits 3 1/4 to 4" boxes, with cage neck. White.

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 Email Print



product gallery

Representative images shown.

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

Top 5 Resources

 [Lampholder \(Instruction Sheet No.\)](#)

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 4.5"

Technical Information

- Volts: 250V
- Watts: 250

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- .

you might like




CordMate Cord Channel

[View Details](#)

resources

INSTRUCTION SHEET NO.

 [LampholderPDF \(68.45kb\)](#)