

L291dGxldC1zdHJhcHMuYXNweGQWAmYPFglfAAV5PGltZyByZXBsYWNIPSJkc3JjliBkc3JjPSlVfi9tZWRpYS80MjFGMDI2QTdBNEQ0REZCOTMyRkE4MTg



designed to be better.

Search

Medium Base Lampholder

288

Medium base, porcelain, pullchain, 2 terminals with tri-drive screws, 15 amp, 125 volt, grounding receptacle, fits 3 1/4" and 4" boxes with cage neck. White.

Submit Query

Where to buy

Submit Query

Like 0 Tweet 0 0 Email Print



product gallery

Representative images shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

Top 5 Resources

 Lampholder (Instruction Sheet No.)

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 4.5"

Technical Information

- Volts: 125V
- Watts: 250

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

resources

INSTRUCTION SHEET NO.

 LampholderPDF (68.45kb)