



designed to be better.

# TradeMaster Receptacle, Black

3232BK

Duplex Grounding Receptacle. 15 amp, 125 volt, Black.

Where to buy

0



Representative image shown.

## AVAILABLE OPTIONS



TradeMaster Receptacle





TradeMaster Receptacle



TradeMaster Receptacle

- SPECIFICATIONS

## features & benefits

- High-impact resistant thermoplastic construction.
- Extra-long strap. Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 - #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

## specifications

### General Info

- Color: Black
- Number Of Poles: 2
- Number Of Wires: 3

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

### Dimensions

- Depth (U S): 0.96"
- Height U S: 3.31"
- Width U S: 1.32"

## Technical Information

- Amps: 15
- Volts: 125
- Volts A C: 125

## Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-