

faGxWaWV3SW1hZ2VMaW5rliBocmVmPSlvZGltbWVycy1zd2l0Y2hlc9tb3Rpb24tc2Vuc29ycy5hc3B4lj48aW1nIHJlcGxhY2U9ImRzcmMilGRzcmM9li9+L211Z



designed to be better.

 Search

TradeMaster Receptacle

3232I

Duplex Grounding Receptacle with high-impact resistant thermoplastic construction. It has ultrasonic welding of face to back body and long-term blade retention. 15 amp, 125 volt. Ivory.

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS



TradeMaster Receptacle



TradeMaster Receptacle, Black



TradeMaster Receptacle

- SPECIFICATIONS

features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping. Extra-large circuit break-off tabs.
- Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only.
- Low profile face. Traditional contoured face. (3232 models) Self-grounding models provide automatic ground clip.

specifications

General Info

- Color: Ivory
- Number Of Poles: 2
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes

- U N S P S C: 39121406

Dimensions

- Depth (U S): 0.96"
- Height U S: 3.31"
- Width U S: 1.32"

Technical Information

- Amps: 15
- Volts: 125
- Volts A C: 125

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-