



designed to be better.

Search

TradeMaster Receptacle

3232W

Duplex Grounding Receptacle with high-impact resistant thermoplastic construction. It has ultrasonic welding of face to back body and long-term blade retention. 15 amp, 125 volt. White.

Where to buy

Like

Tweet





product gallery

Representative images shown.

AVAILABLE OPTIONS



TradeMaster Receptacle, Black



TradeMaster Receptacle



TradeMaster Receptacle

- SPECIFICATIONS

features & benefits

- Extra-long strap. Quickloop wire looping aid. Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs. Side-access push wire release. Side wire accepts #12 - #14 AWG solid wire. Push wire accepts #14 AWG solid only. Low profile face. Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

specifications

General Info

- Color: White
- Number Of Poles: 2
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 0.96"
- Height U S: 3.31"
- Width U S: 1.32"

Technical Information

- Amps: 15
- Volts: 125
- Volts A C: 125

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-