



designed to be better.

[Search](#)

TradeMaster Receptacle

3232

Duplex Grounding Receptacle. 15 amp, 125 volt. Brown.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- SPECIFICATIONS
- YOU MIGHT LIKE

features & benefits

- High-impact resistant thermoplastic construction.
- Extra-long strap. Quickloop wire looping aid.
- Long-term blade retention.
- Longer tri-drive screws for easier #12 AWG looping.
- Extra-large circuit break-off tabs.
- Side-access push wire release.
- Ultrasonic welding of face to back body.
- Side wire accepts #12 - #14 AWG solid wire.
- Push wire accepts #14 AWG solid only.
- Low profile face.
- Traditional contoured face.
- (3232 models) Self-grounding models provide automatic ground clip.

specifications

General Info

- Color: Brown
- Number Of Poles: 2
- Number Of Wires: 3

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 0.96"
- Height U S: 3.31"
- Width U S: 1.32"

Technical Information

- Amps: 15
- Volts: 125
- Volts A C: 125

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

you might like



TradeMaster Decorator Duplex Receptacle, Brown

885

[View Details](#)



Duplex Receptacle Openings, One Gang, Brown

TP8

[View Details](#)