

Specialties Mounting Straps, Yokes & Jewels



Description	Finish	Color	Catalog Number	Dimensions
Mounting Straps & Yokes				
Mounting strap for dimmer insert. Box mounted. Change from decorator to toggle opening.	Painted Steel	Ivory White Brown Light Almond	327I 327W 327 327LA	
Mounting strap for blank insert. Box mounted. Changes decorator opening to blank.	Painted Steel	Ivory White Brown Light Almond	326I 326W 326 326LA	
Tandem mounting strap with two vertical openings. Plate screw hole spacing 4-3/8".	Bright Zinc		342	
Mounting strap with three horizontal openings. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		348	
Mounting strap with single vertical opening. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		347	
Adjustment yoke for strap mounted telephone and blank wall plates. Slots 3-9/32" C to C. Plate screw holes 2-3/8" C to C. Box mounted.	Bright Zinc		340	
Mounting strap for blank insert. Changes toggle opening to blank, box mounted.	Thermoset	Ivory White Light Almond	80700I 80700W 80700LA	

Description	Jewel Color	Catalog Number	Jewels		Jewels Shown with Wall Plates
			Front View	Side View	
Plastic Jewels – For Toggle Switch Openings (Style #1)					
Rectangular acrylic plastic warning light jewel for toggle switch plates with holding ring. Red Jewel Standard.	Red Green White	406RED 406GN 406W			
Plastic Jewels – For Single Receptacle Openings (Style #7)					
Round acrylic plastic warning light jewel for single receptacle plates with holding ring. Red Jewel Standard.	Red Green White	405RED 405GN 405W			

UL Listed.