

xYCHwQFMS9pbnRlcmNvbXMtYW5kLWRvb3ltZW50cnkvYnJvYWRjYXN0LWludGVyY29tLmFzchhkFjCAQ8WAh8ABRJCCm9hZGNhc3QgSW50ZXJjb21kA



designed to be better.

Search

Medium Base Lampholder

3352F

Medium base, porcelain, keyless, screw terminals, short base. White.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter Metric: 1.38"
- Height U S: 2.00"

Technical Information

- Volts: 250V
- Volts A C: 250
- Watts: 660

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No