

PSlyMTgilGhlaWdodD0iMTEyliAvPjwvYT4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAyX3JwdENvbW1lcmNpYWxfY3RsMDNfcnB0Q29tbWVvY2lhbF



designed to be better.

Search

Corrosion-Resistant Receptacle

3771

2pole 3wire 600volt Ac 250volt Dc Receptacle

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

features & benefits

- Quality Materials, durability, and time-tested design

specifications

General Info

- Type: Receptacle
- Number Of Wires: 3
- Special Features: Corrosion-Resistant

Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.08"
- Diameter U S: 1.98"
- Height U S: 3.28"

Technical Information

- Amps: 50 Amp
- Volts: 250VDC, 600VAC
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant

