

Q8PFglfBAUjL29yZ2FuaXplLWNvcnRzL29uLXdhbGwtd2lyaW5nLmFzcHhkFgICAQ8WAh8ABQ5Pbi1XYWxsIFdpcmnuZ2QCAw9kFgQCAQ8PFglfBAUWL2Rf



designed to be better.

Search

Hospital Grade Quad Receptacles

420HI

Hospital Grade Quad Receptacle 20amp 125volt Ivory

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print





•



•

product gallery

Representative images shown.

AVAILABLE OPTIONS



Hospital Grade Quad Receptacle, White



Hospital Grade Quad Receptacles



Hospital Grade Quad Receptacles





Hospital Grade Quad Receptacles

- SPECIFICATIONS
- RESOURCES

features & benefits

- Rugged nylon face and body withstands impacts and hard use.
- Built-in wire stripping gauge.
- Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.
- Heavy-duty, phosphor bronze contacts.
- Shielding walls guard against live-circuit-to-ground shorts.
- Split circuit break-off tabs.
- UL and CSA listed.

Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Quad Receptacle \(Instruction Sheet No.\)](#)

specifications

General Info

- Color: ivory
- Type: Quad, Receptacles
- Special Features: Split Circuit

Listing Agencies/Third Party Information

- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Height U S: 4.5"
- Width U S: 4.5"

Technical Information

- Amps: 20
- Volts: 125V
- Volts A C: 125
- Capacity: Quad
- Grade Type: Hospital

Buy American Act Compliance


- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources
BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

INSTRUCTION SHEET NO.

 Quad ReceptaclePDF (211.62kb)