

xpPiA8bGkgY2xhc3M9ImNvbDliPiA8YSBpZD0iY3RsMDVfTFpdk5hdjFfY3RsMDFfcnB0UmVzaWRlbnRpYWxfY3RsMTRfcnB0UmVzaWRlbnRpYWxTdWJtZ



designed to be better.

 Search

15 Amp NEMA L615 Single Receptacle

4560

Receptacle Single 15amp 250volt Turnlok

Where to buy

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Turnlok Heavy Duty Receptacles, SF1701R1 (Cutsheet)

specifications

General Info

- Type: Single, Receptacles

Listing Agencies/Third Party Information

- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): .922"
- Diameter U S: 1.375"
- Height U S: 3.281"

Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L615
- Volts: 250V
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Turnlok Heavy Duty Receptacles, SF1701R1PDF \(235.57kb\)](#)