

ylIvPmQCBQ8PFglfBAUcL2F1ZGivLXZpZGVvL2F1ZGivLWtpdHMuYXNweGQWAgIBDxYCHwAFCKF1ZGivIEtpdHNkAgMPZBYGAgEPDxYCHwQFKi9hdWI



designed to be better.

Search

## 15 Amp NEMA L715 Single Receptacle

4760

Turnlok Single Receptacle 3wire 15amp 277v

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Turnlok Heavy Duty Receptacles, SF1701R1 (Cutsheet)

### specifications

#### General Info

- Type: Single, Receptacles
- Number Of Wires: 3

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

#### Dimensions

- Depth (U S): 1.203"
- Height U S: 4.031"
- Width U S: 1.437"

#### Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L715
- Volts: 277V
- Volts A C: 277

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



**resources**  
**BROCHURE**

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

**CUTSHEET**

 [Turnlok Heavy Duty Receptacles, SF1701R1PDF \(235.57kb\)](#)