



designed to be better.

15 Amp NEMA L515 Combination Straight Blade and Locking

4792

Receptacle Duplex Combination

Where to buy

0





Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Compact, impact-resistant nylon face and body are ultrasonically welded together for unrivaled strength.
- Face color coding by voltage facilitates locating and mating of proper devices.
- One piece, high-grade brass contacts offer excellent conductivity and heat-rise resistance.
- Clearly marked NEMA configuration, rating, and third-party listing on each unit's face.
- Single-piece, solid brass mounting strap is free of easily loosened rivets found on other brands.
- Side and external screw-pressure-plate back wire capability.
- Accepts #14 - #10 AWG.

Top 5 Resources

-  Commercial & Industrial Products (Brochure)
-  Turnlok Heavy Duty Receptacles, SF1701R1 (Cutsheet)

specifications

General Info

- Type: Combination, straight blade, locking

Listing Agencies/Third Party Information

- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): 1.199"
- Height U S: 3.28"
- Width U S: 1.50"

Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L515

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant
- .



resources BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)

CUTSHEET

-  Turnlok Heavy Duty Receptacles, SF1701R1PDF (235.57kb)