



designed to be better.

Surge Protective Duplex Receptacle, Ivory

5252ISP

Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (LED Indicator only). Back & Side Wire, 15amp 125volt, Ivory.

Where to buy

Like



product gallery

Representative images shown.

AVAILABLE OPTIONS








- RELATED PRODUCTS
- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

features & benefits

- **Solid-state LED monitor** has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.
- **LED Indication:** Steady green = protected, Flashing re = not protected, OFF = no power to unit
- **Wrap-around steel strap** for structural integrity. Auto-ground is standard, for easier installation.
- **Impact-resistant thermoplastic exterior** resists impacts and scrapes.
- **Triple-wipe, copper-alloy contacts** for superior, more dependable connection.
- **External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive)** accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors. External pressure plate feature allows two conductors to be terminated by a single screw.
- **Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules** of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.

Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Surge Protective Receptacles, SF1305R1 \(Cutsheet\)](#)
-  [Surge Protective Devices \(Installation Instructions\)](#)

related products



Decorator Openings, One Gang, 302 Stainless Steel

SS26

[View Details](#)



Surge Protective Power Strip 7 Outlet, PC Gray

PS7

[View Details](#)

specifications

General Info

- Color: Ivory
- Type: Duplex
- Special Features: Surge-Protective

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.225" (Behind Strap)
- Height U S: 3.82"
- Width U S: 1.750"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
-

you might like



Panel TVSS Unit, Heavy Duty

1220TWH

[View Details](#)



Extra-Hard Use (EHU) Specification Grade Plug, Black & White


PS5266X

[View Details](#)

resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Surge Protective Receptacles, SF1305R1PDF \(146.38kb\)](#)

INSTALLATION INSTRUCTIONS

 [Surge Protective DevicesPDF \(497.67kb\)](#)