

bWVudS1jb250ZW50IC0tPiA8L2xpPiA8bGkgY2xhc3M9Im1lZ2EgbGFzdCIgaWQ9Im1lbnUtbGktcmVzb3VyY2Vzlj4gPGg0PjxhIGhyZWY9IiMilGNsYXNzPSJtY



designed to be better.

Search

## Specification Grade Surge Protective Duplex Receptacle, White

5262WSP

Extra Heavy-Duty Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back & Side Wire, 15amp 125volt, White.

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

0

Email Print



### product gallery

Representative images shown.

### AVAILABLE OPTIONS





Specification Grade Surge Protective Duplex Receptacle, Black



Specification Grade Surge Protective Duplex Receptacle, Blue



Specification Grade Surge Protective Duplex Receptacle, Gray



Specification Grade Surge Protective Duplex Receptacle, Ivory



Specification Grade Surge Protective Duplex Receptacle, Light Almond



Specification Grade Surge Protective Duplex Receptacle, Red



Specification Grade Surge Protective Duplex Receptacle, Brown

- RELATED PRODUCTS
- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

## features & benefits

- **Solid-state LED monitor** has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.
- **LED Indication:** Steady green = protected, Flashing red = not protected, OFF = no power to unit
- **Audible alarm alert** of MOV damage. Alarm able to be turned On/Off.
- **Wrap-around steel strap** for structural integrity. Auto-ground is standard, for easier installation.
- **Impact-resistant thermoplastic exterior** resists impacts and scrapes.
- **Triple-wipe, copper-alloy contacts** for superior, more dependable connection.
- **External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive)** accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors. External pressure plate feature allows two conductors to be terminated by a single screw.
- **Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules** of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection. Protection response time in less than one nanosecond.

## Top 5 Resources

- [Commercial & Industrial Products \(Brochure\)](#)
- [Heavy Duty Surge Protective Receptacles, SF1304R1 \(Cutsheet\)](#)
- [Surge Protective Devices \(Installation Instructions\)](#)

**related products****Decorator Openings, One Gang, 302 Stainless Steel**

SS26

[View Details](#)**Surge Protective Power Strip 7 Outlet, PC Gray**

PS7

[View Details](#)**specifications****General Info**

- Color: White
- Type: Duplex
- Duty: Extra Heavy Duty
- Special Features: Audible Alarm with LED Monitor, Isolated Ground

**Listing Agencies/Third Party Information**

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

**Dimensions**

- Depth (U S): 1.225" (Behind Strap)
- Height U S: 3.82"
- Width U S: 1.750"

**Technical Information**

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Grade Type: Specification

**Buy American Act Compliance**

- Country of Origin: CHINA
- Buy American Act Status: No

**you might like****Panel TVSS Unit, Heavy Duty**

1220TWH

[View Details](#)



**Extra-Hard Use (EHU) Specification Grade Plug, Black & White**

PS5266X

[View Details](#)

**resources**

**BROCHURE**

[Commercial & Industrial Products](#)PDF (3.52mb)

**CUTSHEET**

[Heavy Duty Surge Protective Receptacles, SF1304R1](#)PDF (148.7kb)

**INSTALLATION INSTRUCTIONS**

[Surge Protective Devices](#)PDF (497.67kb)