

nN0YWxsYXRpb24tdG9vbHMuYXNweGQWAgIBDxYCHwAFHkxvdyBWB2x0YWdlIEluc3RhbGxhdGlvbiBUb29sc2QCAw9kFgYCAQ8PFglfBAUkL3N0cnVjdHl



designed to be better.

Search

Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory

5362AI

Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Ivory

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, White



Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Brown



Industrial Extra Heavy-Duty Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Black



Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Blue



Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond




Industrial Extra Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- One-piece brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .036 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 -- #10 AWG stranded or solid copper clad conductors.
- Auto-ground clip assures positive ground.
- Corrosion-resistant models have nickel-plated straps and contacts.

Top 5 Resources

-  Extra Heavy Duty Receptacles, SF301R1 (Cutsheet)

specifications

General Info

- Color: Ivory
- Type: Receptacles
- Duty: Extra Heavy Duty
- Special Features: Back, Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .900"
- Height U S: 3.281"
- Width U S: 1.625"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Industrial

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

CUTSHEET

-  Extra Heavy Duty Receptacles, SF301R1PDF (495.76kb)