

NvbXMgJiBEb29ylEVudHJ5PC9hPiA8dWwgY2xhc3M9ImhpZGUtbnV3lj4gPGxpIGNsYXNzPSJjb2wylj4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAX)



designed to be better.

Search

Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Gray

5362GRY

Hard Use Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Gray

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, White



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Brown



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Black



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Blue



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Green





Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Ivory



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Light Almond



Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

features & benefits

- Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Hard Use Receptacles, SF310R1 (Cutsheet)

specifications

General Info

- Color: gray
- Type: Receptacles
- Special Features: Back, Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .780"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant



you might like



863 Series Wood Floor Boxes

863

[View Details](#)



WMFB Single- or Multi-Service Residential Wood Floor Box


WMFB

[View Details](#)

resources
BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

CUTSHEET

 [Hard Use Receptacles, SF310R1PDF \(146.48kb\)](#)