

mZvdXJ0aC1sdmWgY29sMyI+IDxhIGlkPSJjdGwwNV9NYWluTmF2MV9jdGwwMV9ycHRSZXNpZGVudGlhbF9jdGwwN19ycHRSZXNpZGVudGlhbFN1Ym1lbr



designed to be better.

Search

Heavy-Duty Spec Grade Single Receptacles, Side Wire, 15A, 250V, Ivory

5651I

Heavy-Duty Spec Grade Single Receptacle Side Wire 15amp 250volt Ivory

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Heavy-Duty Spec Grade Single Receptacles, Side Wire, 15A, 250V, White

Heavy-Duty Spec Grade Single Receptacles, Side Wire, 15A, 250V, Light Almond

- SPECIFICATIONS

features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.

specifications

General Info

- Color: Ivory
- Type: Single,Receptacles
- Duty: Heavy Duty
- Special Features: Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 1.08"
- Height U S: 3.28"
- Width U S: 1.32"

Technical Information

- Amps: 15 Amp
- Volts: 250V
- Volts A C: 250
- Capacity: Single
- Grade Type: Federal Specification

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

