

HgftfUI0ZW1Db3VudAIFfGpmD2QWBAIFDxYCHwBIZAIHDw8WAh4LTmF2aWdhGVVcmwFDi9jYWJsb2ZpbC5hc3B4ZBYCZg8WAh8ABaQBPGItZyBtZWRF



designed to be better.

Search

# Heavy-Duty Spec Grade Single Receptacle, Side Wire, 20A, 250V, Ivory

5851I

Heavy-Duty Spec Grade Single Receptacle, Side Wire 20amp 250volt, Ivory

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

## AVAILABLE OPTIONS



Heavy-Duty Spec Grade Single Receptacles, Side Wire, 20A, 250V, White



Heavy-Duty Spec Grade Single Receptacles, Side Wire, 20A, 250V, Brown



Heavy-Duty Spec Grade Single Receptacles, Side Wire, 20A, 250V, Light Almond

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Auto-ground clip assures positive ground.
- Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.
- Heavy-duty, corrosion-resistant zinc-plated steel strap for added strength.
- Backed-out tr-drive steel terminal screws. Internal screw-pressure-plate back and side wire capability. Two back wire holes for increased wiring flexibility.
- One-piece brass triple-wire power contacts for lasting retention.

## Top 5 Resources

Commercial & Industrial Products (Brochure)

## specifications

### General Info

- Color: Ivory
- Type: Single,Receptacles
- Duty: Heavy Duty
- Special Features: Side Wire

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 1.08"
- Height U S: 3.28"
- Width U S: 1.380"

#### Technical Information


- Amps: 20 Amp
- Volts: 250V
- Volts A C: 250
- Capacity: Single
- Grade Type: Federal Specification

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



#### resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)