

9+L21IZGIhLONEQTA0M0QzRTQ3QzRCNjZCQzUyQ0lwMzI4NDc2ODhBLmFzaHgilGFsdD0tTG93IFZvbHRhZ2UgQnJhY2tldHMlIHdpZHRoPSlyMTgilGhlaWk=



designed to be better.

Search

# Heavy-Duty Spec Grade Single Receptacles, Back & Side Wire, 20A, 250V, Brown

5871

Heavy-Duty Spec Grade Single Receptacle Back & Side Wire 20amp 250volt Brown

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## specifications

### General Info

- Color: brown
- Type: Single,Receptacles
- Duty: Heavy Duty
- Special Features: Back,Side Wire

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

### Dimensions

- Depth (U S): 1.093"
- Height U S: 3.28"
- Width U S: 1.32"

### Technical Information

- Amps: 20 Amp
- Volts: 250V
- Volts A C: 250
- Capacity: Single
- Grade Type: Federal Specification

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant

