

LWF2L2ZpcmVzdG9wLWZpdHRpbmdzLmFzcHgiPIZpZXcgRmlyZXN0b3AgRml0dGluZ3M8L2E+IDwvZGI2PiA8L2xpPiA8bGkgY2xhc3M9ImNvbDIiPiA8YSBpZ



designed to be better.

[Search](#)

TradeMaster Grounding Toggle Switch

660G

Single Pole Switch, Grounded Terminals, 15 amps, 120 volts, Brown.

*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660GU

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS



TradeMaster Grounding Toggle Switch, White

- SPECIFICATIONS

features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

specifications

General Info

- Product Series: TradeMaster
- Type: Toggle
- Number Of Poles: 1
- Special Features: Self-Grounding

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 1.090"
- Height U S: 3.281"
- Width U S: 1.25"

Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: Trade Agreement Act Compliant
-