

ZAIDDw8WAh8EBS8vZWxIY3RyaWNhbC1hY2Nlc3Nvcmlcy93YWxsLXBsYXRILWluc2VydHMuYXNweGQWAmYPFglfAAV+PGltZyByZXBsYWNIPSJkc3JjliB



designed to be better.

[Search](#)

## TradeMaster Grounding Toggle Switch, Light Almond

660LAG

Single Pole Switch in light almond with grounded terminals, is made with a thermoplastic toggle and frame. It has a smooth, quiet toggle action. It is made with high-impact resistant construction. 15 amps, 120 volts.

\*Available in bulk packs of 120. Add "U" to end of Catalog Number. Example: 660LAGU



Representative image shown.

- [SPECIFICATIONS](#)

### features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

### specifications

#### General Info

- Product Series: TradeMaster
- Type: Toggle
- Number Of Poles: 1
- Special Features: Self-Grounding

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121406

#### Dimensions

- Depth (U S): 1.090"
- Height U S: 3.281"
- Width U S: 1.25"

#### Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120

#### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: Trade Agreement Act Compliant