



designed to be better.

Search

TradeMaster Grounding Toggle Switch, Brown

663G

Triple Pole Switch, Grounded Terminals, 15 amps, 120 volts, Brown.

**Available in bulk packs of 90. Add "U" to end of catalog number. Example: 663GU

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



TradeMaster Grounding Toggle Switch, Ivory


- SPECIFICATIONS

- RESOURCES

features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

Top 5 Resources

-  NAFTA Compliant Residential Devices (Supporting Document)

specifications

General Info

- Product Series: TradeMaster
- Type: Toggle
- Number Of Poles: 3-way
- Special Features: Self-Grounding

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 1.090"
- Height U S: 3.281"
- Width U S: 1.25"

Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

SUPPORTING DOCUMENT

-  NAFTA Compliant Residential DevicesPDF (366.4kb)

