

tc3dpdGNoZXMuYXNweCI+VmlldyBFbGVjdHJpY2FsIFN3aXRjaGVzPC9hPiA8L2Rpdj4gPC9saT4gPGxpIGNsYXNzPSJjb2wyIj4gPGEgaWQ9ImN0bDA1X01f



designed to be better.

 Search

TradeMaster Grounding Toggle Switch, Ivory

663IG

Triple Pole Switch in ivory with grounded terminals, has a thermoplastic toggle and frame. It has a smooth, quiet toggle action and is made with high-impact resistant construction. 15 amps, 120 volts.

**Available in bulk packs of 90. Add "U" to end of Catalog Number. Example: 663IGU

 Submit Query
Where to buy Enter Postal Code
 Submit Query

0



Representative image shown.

AVAILABLE OPTIONS



TradeMaster Grounding Toggle Switch, White



TradeMaster Grounding Toggle Switch, Black



TradeMaster Grounding Toggle Switch, Ivory



TradeMaster Grounding Toggle Switch, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.