

uZyIgd2lkdGg9IjlxOC1gaGVpZ2h0PSIxMTIiIC8+ZAIFDw8WAh8EBTYvY2FiaW5ldC1saWdodGluZy1wb3dldCI91bmRlci1jYWltbGlnaHRpbmctc3lzdGVtLmFzcHh



designed to be better.

[Search](#)

TradeMaster Grounding Toggle Switch

663WSLG

Three-Way Lighted Toggle Switch, 15 amps 120 volts, White.

[Submit Query](#)

Where to buy

[Submit Query](#)

0



Representative image shown.

AVAILABLE OPTIONS



TradeMaster Grounding Toggle Switch



TradeMaster Grounding Toggle Switch

- SPECIFICATIONS

features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

specifications

General Info

- Product Series: TradeMaster
- Type: Toggle
- Number Of Poles: 3-way
- Special Features: Self-Grounding

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 1.090"
- Height U S: 3.281"
- Width U S: 1.25"

Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

