

3NEVBQy5hc2h4liBhbHQ9IkNhYmxlIFRyYXkgLSBXaXJlIE1lc2gllHdpZHRoPSlyMTgilGhlaWdodD0iMTEyIiAvPmQCBQ8PFglfBAUoL2NvbW1lcmNpYWwtYX'



designed to be better.

Search

# TradeMaster Grounding Toggle Switch, White

664WG

Four-Way Switch, Grounded Terminals, 15 amps, 120 volts, White.

Submit Query

Where to buy  Enter Postal Code   0

[Email](#) [Print](#)



Representative image shown.

## AVAILABLE OPTIONS



TradeMaster Grounding Toggle Switch, Black



TradeMaster Grounding Toggle Switch, Brown



TradeMaster Grounding Toggle Switch, Ivory




TradeMaster Grounding Toggle Switch, Light Almond

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Side wire #12 and #14 AWG. Push wire #14 AWG.
- Tri-drive ground, terminal, and mounting screws.
- Easy-access green hex head ground screw.

### Top 5 Resources

 [NAFTA Compliant Residential Devices \(Supporting Document\)](#)

### specifications

#### General Info

- Product Series: TradeMaster
- Type: Toggle
- Number Of Poles: 4-way
- Special Features: Self-Grounding

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 111
- CSA Standard: Yes
- UL Listing No: 20
- UL Standard: Yes
- U N SPS C: 39121406

#### Dimensions

- Depth (U S): 1.090"
- Height U S: 3.281"
- Width U S: 1.25"

#### Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 120

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



### resources

#### SUPPORTING DOCUMENT

 [NAFTA Compliant Residential DevicesPDF \(366.4kb\)](#)