

pPiA8bGkgY2xhc3M9ImZpcnN0Ij4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAzX3JwdFJlc2lkZW50aWFsX2N0bDAX2hsU29sdXRpb24iIGhyZWY9IiE



designed to be better.

Search

# Combination Switches

691I

Single Pole Switch, Single Receptacle Combination Switch, 15 amps, 120/125 volts, Ivory.

Submit Query  Enter Postal Code  Submit Query

[Email](#) [Print](#)



Representative image shown.

## AVAILABLE OPTIONS

- 
- 
- 
- 
- 
- 

- SPECIFICATIONS

### features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

### specifications

#### General Info

- Type: Standard

#### Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes

- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

**Dimensions**

- Depth (U S): 1.15"
- Height U S: 3.28"
- Width U S: 1.32"

**Technical Information**

- Volts A C: 125

**Buy American Act Compliance**

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 

