



designed to be better.

Search

# Combination Switch

691TRW

Single Pole Switch, Tamper-Resistant Receptacle. 15 amps, 120 volts, White.

Where to buy

0



Representative image shown.

## AVAILABLE OPTIONS




- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

## features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

## Top 5 Resources

-  Tamper-Resistant Receptacles (Brochure)

## specifications

### General Info

- Type: Tamper-Resistant

## Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: No
- U N SPS C: 39121406
- U R: No

## Dimensions

- Depth (U S): 1.15"
- Height U S: 3.69"
- Width U S: 1.32"

## Technical Information

- Amps: 15 Amp
- Volts A C: 120

## Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



## you might like



### **CordMate II Cord Channel**

[View Details](#)



### **Nonmetallic Raceway**

[View Details](#)

## **resources** **BROCHURE**

 [Tamper-Resistant ReceptaclesPDF \(791.69kb\)](#)