



designed to be better.

Non-Grounding Combination Switches

692I

Single Pole, Single Pilot Light, Combination Switch, 15 amps, 120/125 volts, Ivory.

Where to buy

0



Representative image shown.

AVAILABLE OPTIONS



Non-Grounding Combination Switches





Non-Grounding Combination Switches



Non-Grounding Combination Switches



Non-Grounding Combination Switches

- SPECIFICATIONS

features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

specifications

General Info

- Type: Combination, Pilot Light
- Number Of Poles: 1
- Special Features: Non-Grounding

Listing Agencies/Third Party Information

- UL Listing No: 20; 498
- UL Standard: Yes
- U N SPS C: 39121406

Dimensions

- Depth (U S): 0.94"
- Height U S: 3.28"
- Width U S: 1.32"

Technical Information

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 250

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-

