

UaGVhdGVyZAIgD2QWBgIBDw8WAh8EBRovYXVkaW8tdmklZW8vc3BIYWtlcnMuYXNweGQWAmYPFglfAAUIU3BIYWtlcnNkAgMPDxYCHwQFGi9hdWRpb



designed to be better.

[Search](#)

# Non-Grounding Combination Switches

695W

Three-way, Single Pilot Light, Combination Switch, 15 amps, 120/125 volts, White.

[Email](#) [Print](#)



Representative image shown.

## AVAILABLE OPTIONS



Non-Grounding Combination Switches



Non-Grounding Combination Switches



Non-Grounding Combination Switches

- SPECIFICATIONS

### features & benefits

- Easily accessible break-off separate or common feed.
- Long-life red neon lamp in pilot light rated 1/25 Watt, 125V.
- Side wire #12 and #14 AWG.
- Two devices fit into the space of one.
- Grounding combination devices meet NEC Requirements.
- Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

### specifications

#### General Info

- Type: Combination, Pilot Light
- Number Of Poles: 3-way
- Special Features: Non-Grounding

#### Listing Agencies/Third Party Information

- UL Listing No: 20

- UL Standard: Yes
- U N SPS C: 39121406

**Dimensions**

- Depth (U S): 0.94"
- Height U S: 3.28"
- Width U S: 1.32"

**Technical Information**

- Amps: 15 Amp
- Volts: 120VAC
- Volts A C: 125

**Buy American Act Compliance**

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 

