



designed to be better.

[Search](#)

# 20 Amp Non-NEMA Plug - Black Back, White Front Body

7411SS

Turnlok Plug 4wire 20amp 3phase 120/208v

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)




Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

## features & benefits

- Quick-thread assembly screws and cord-grip screws come backed-out, ready-to-wire.
- Industrial-strength, brass alloy plug blades and connector contacts resist heat rise, provide excellent conductivity.
- Raised ribs provide non-slip gripping profile for turning to lock and unlock.
- Double dovetail design provides superior protection against cord pull-out forces.
- Impact- and corrosion-resistant durable nylon 6/6 shell material.
- Rounded back contour reduces snags and hang-ups on the job site.
- Scallop shell design provides non-slip gripping surface for insertion and withdrawal.
- Visible stamped NEMA configuration and device rating.
- New-design external cord grips provide visible assurance of safe and proper cord retention.
- Integral flexible rubber cord grommet conforms to and seals around SO cord to provide protection from oils, water, or chips entering wiring chamber.

## Top 5 Resources

 Commercial & Industrial Products (Brochure)

## specifications

### General Info

- Color: Black, White
- Type: Plug
- Number Of Wires: 4
- Special Features: Non-Nema

## Listing Agencies/Third Party Information

- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

## Dimensions

- Diameter U S: 2.20"
- Length: 3.75"

## Technical Information

- Amps: 20 Amp
- Volts: 120/208V
- Volts A C: 120/208

## Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



## resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)