



designed to be better.

[Search](#)

15 Amp NEMA L115 Single Receptacle

7535

Receptacle Single 15amp 125volt Turnlok

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

- [SPECIFICATIONS](#)
- [RESOURCES](#)

features & benefits

- Interior components constructed of high-grade brass material for physical and electrical integrity.
- High-impact thermoplastic housing withstands on-the-job abuse.
- Ratings and NEMA configurations are clearly visible on flange face, for fast I.D. while in use.

Top 5 Resources

[Commercial & Industrial Products \(Brochure\)](#)

specifications

General Info

- Type: Duplex, Receptacles

Listing Agencies/Third Party Information

- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Depth (U S): .922"
- Height U S: 3.281"
- Width U S: 1.562"

Technical Information

- Amps: 15 Amp
- NEMA Configuration Number: L115
- Volts: 125V
- Volts A C: 125

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Buy American Act Compliant
-



resources BROCHURE

 [Commercial & Industrial ProductsPDF \(3.52mb\)](#)