

RsMDJfcnB0Q29tbWVvY2lhbFN1Ym1lbnVfY3RsMDZfaGxWaWVv3TGlualyY2xhc3M9InZpZXctbW9yZSIgaHJlZj0iL2VsZWNOcmliYWwtd2lyaW5nLWRldmliZjZ



designed to be better.

Search

Medium Base Lampholder

8052CC10

medium base, porcelain, bracket mount.

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: No
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 2.31"

Technical Information

- Volts: 250V
- Watts: 660

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No