

Specialties Mounting Straps, Yokes & Jewels

Pass & Seymour



Description	Finish	Color	Catalog Number	Dimensions
Mounting Straps & Yokes				
Mounting strap for dimmer insert. Box mounted. Change from decorator to toggle opening.	Painted Steel	Ivory White Brown Light Almond	327-I 327-W 327 327-LA	
Mounting strap for blank insert. Box mounted. Changes decorator opening to blank.	Painted Steel	Ivory White Brown Light Almond	326-I 326-W 326 326-LA	
Tandem mounting strap with two vertical openings. Plate screw hole spacing 4-3/8".	Bright Zinc		342	
Mounting strap with three horizontal openings. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		348	
Mounting strap with single vertical opening. Plate screw hole spacing 3-13/16". Box mounted.	Bright Zinc		347	
Adjustment yoke for strap mounted telephone and blank wall plates. Slots 3-9/32" C to C. Plate screw holes 2-3/8" C to C. Box mounted.	Bright Zinc		340	
Mounting strap for blank insert. Changes toggle opening to blank, box mounted.	Thermoset	Ivory White Light Almond	80700-I 80700-W 80700-LA	

Description	Jewel Color	Catalog Number	Jewels		Jewels Shown with Wall Plates
			Front View	Side View	
Plastic Jewels – For Toggle Switch Openings (Style #1)					
Rectangular acrylic plastic warning light jewel for toggle switch plates with holding ring. Red Jewel Standard.	Red Green White	406-RED 406-GN 406-W			
Plastic Jewels – For Single Receptacle Openings (Style #7)					
Round acrylic plastic warning light jewel for single receptacle plates with holding ring. Red Jewel Standard.	Red Green White	405-RED 405-GN 405-W			

UL Listed.