

iA8YSBpZD0iY3RsMDVfTWFpbk5hdjFfY3RsMDJfcnB0Q29tbWVvY2lhbF9jdGwwMI9ycHRDb21tZXJjaWFsU3VibWVudV9jdGwxMI9obFZpZXdMaW5rliBjbGF:



designed to be better.

Search

Medium Base Lampholder

8101

Medium base, porcelain, keyless, single circuit, 2 peice ring with leads. 1 3/8" to 1 1/2" hole. White.

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Quality Materials.
- Durability.
- Time-tested design.

Top 5 Resources

Commercial & Industrial Products (Brochure)

specifications

General Info

- Type: Incandescent Medium Base Lampholder

Listing Agencies/Third Party Information

- CSA Listing Info: Yes
- CUL Listing No: No
- cU Lus: No
- cU Rus: No
- Federal Spec: No
- UL Listing No: Yes
- U N SPS C: 39111803
- U R: No

Dimensions

- Diameter U S: 1.75"

Technical Information

- Volts: 250V
- Volts A C: 250
- Watts: 660

Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: Buy American Act Compliant
-

resources

BROCHURE

Commercial & Industrial ProductsPDF (3.52mb)

