

lhbFN1Ym1lbnVfY3RsMDRfaGxWaWV3TGluaylgY2xhc3M9InZpZXBW9yZSIsaHJlZj0iL2RpbW1lcnMtc3dpdGNoZXMvbGlnaHQtc3dpdGNoZXMuYXNweCI+



designed to be better.

Search

# Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Red

8300HRED

Heavy-Duty Hospital Grade Compact Design Duplex Receptacle Back & Side Wire 20amp 125volt Red

Submit Query

Where to buy Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

## AVAILABLE OPTIONS



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, White



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Brown



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Black



Heavy-Duty Hospital Grade Compact Design Receptacle, Back & Side Wire, 20A, 125V, Gray



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Ivory



Heavy-Duty Hospital Grade Compact Design Receptacles, Back & Side Wire, 20A, 125V, Light Almond

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Impact-resistant nylon face.
- One-piece heat-treated triple-wipe brass power contacts.
- Easily accessible break-off line contact connecting tab for split circuit wiring.
- Corrosion-resistant, zinc-plated steel strap is locked in.
- Internal screw-pressure-plate back wire and side wire line terminals accept #14 – #10 AWG copper or copper-clad conductors.
- High strength thermoplastic back body.
- Back wire holes allow entry of conductor insulation partially into body but not into wiring compartment.
- Auto-ground clip assures positive ground.
- Compact design for easy installation.
- Tri-drive terminal and mounting screws.

### Top 5 Resources

- HG Heavy Duty Compact Design Receptacles, SF706R1 (Cutsheet)

### specifications

#### General Info

- Color: red
- Type: Compact Design,Receptacles
- Duty: Heavy Duty
- Special Features: Back,Side Wire

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

### Dimensions

- Depth (U S): .780"
- Height U S: 3.281"
- Width U S: 1.322"

### Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital

### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



### resources

#### CUTSHEET

- HG Heavy Duty Compact Design Receptacles, SF706R1PDF (151.55kb)