

mQCAg9kFgYCAQ8PFglfBAUvL2VsZWN0cmliYWwtYWNjZXNzb3JpZXMvYXBwbGlhbmNILXN3aXRjaGVzLmFzcHhkFgJmDxYCHwAFEkFwcGxpYW5jZSBT



designed to be better.

[Search](#)

Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Brown

8300
Extra Heavy-Duty Hospital Grade Duplex Receptacle Back & Side Wire 20amp 125volt Brown

[Email](#) [Print](#)



Representative image shown.

AVAILABLE OPTIONS



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, White



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Black



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Gray



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Light Almond



Extra Heavy-Duty Hospital Grade Receptacles, Back & Side Wire, 20A, 125V, Red

- SPECIFICATIONS
- YOU MIGHT LIKE
- RESOURCES

features & benefits

- One-piece nickel-plated brass mounting strap with integral ground.
- Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
- Two drive screws anchor strap to back body and face.
- Exclusive patented feature, circuit label on face allows permanent circuit identification.
- .040 inch thick, nickel-plated brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and back body.
- Oversized #10 deep tri-drive head brass terminal and ground screws.
- Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.
- External nickel-plated screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.
- Line terminals accept #14 - #10 AWG stranded or solid copper-clad conductors.
- Auto-ground clip assures positive ground.
- Illuminated version features exclusive LED lamp with solder connection for long durable life (10-12 years).

Top 5 Resources

- Hospital Grade Extra Heavy Duty Receptacles, SF701R1 (Cutsheet)

specifications

General Info

- Color: brown
- Type: Receptacles
- Duty: Extra Heavy Duty
- Special Features: Back,Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): .900"
- Height U S: 3.281"
- Width U S: 1.625"

Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Hospital

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



you might like



PlugTail™ Extra Heavy-Duty Hospital Grade Receptacles, 20A, 125V, Brown

PT8300


[View Details](#)



Duplex Receptacle Openings, One Gang, 302 Stainless Steel

SS8
[View Details](#)

resources
CUTSHEET

 [Hospital Grade Extra Heavy Duty Receptacles, SF701R1PDF \(153.21kb\)](#)