

cy5hc3B4lj5MaWdodGluZyBDb250cm9sczwwYT4gPGRpdjBjbGFzc0Zm91cnRoLWx2bCBjb2wzlj4gPGEgaWQ9ImN0bDA1X01haW5OYXYxX2N0bDAyX3Jw



designed to be better.

# Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Ivory

83011  
Heavy-Duty Hospital Grade Single Receptacle Back & Side Wire 20amp 125volt Ivory

[Submit Query](#)

Where to buy

[Submit Query](#)

[Email](#) [Print](#)



Representative image shown.

## AVAILABLE OPTIONS



Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, White



Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Brown



Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Gray



Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Red



- SPECIFICATIONS
- RESOURCES

## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

### Top 5 Resources

-  [Commercial & Industrial Products \(Brochure\)](#)
-  [Hospital Grade Heavy Duty Single Receptacles, SF702R1 \(Cutsheet\)](#)

### specifications

#### General Info

- Color: Ivory
- Type: Single, Receptacle
- Duty: Heavy Duty
- Special Features: Back, Side Wire

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- cUL Standard: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 1.093"
- Height U S: 3.28"
- Width U S: 1.32"

#### Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Single
- Grade Type: Hospital

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



#### resources BROCHURE

-  [Commercial & Industrial ProductsPDF \(3.52mb\)](#)

#### CUTSHEET

-  [Hospital Grade Heavy Duty Single Receptacles, SF702R1PDF \(146.18kb\)](#)