

QBPGItZyBtZWRpYWlkaPSJ7RjJGRDY5ODgtNjUwMy00MDg4LTk5MzItMEJFMDFCODUxMjRlBfSlgbWVkaWFwYXRoPSlVSW1hZ2ZvZL05hdmInYXRpb24vV2I



designed to be better.

Search

# Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Red

8301RED

Heavy-Duty Hospital Grade Single Receptacle Back & Side Wire 20amp 125volt Red

Submit Query

Where to buy

Submit Query

Like 0

Tweet 0

Email Print





## product gallery

Representative images shown.

### AVAILABLE OPTIONS

Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, White

Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Brown

Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Gray

Heavy-Duty Hospital Grade Single Receptacles, Back & Side Wire, 20A, 125V, Ivory

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- One-piece brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Internal screw-pressure-plate back wire capable of accepting #14 – #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

### Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Hospital Grade Heavy Duty Single Receptacles, SF702R1 (Cutsheet)

### specifications

#### General Info

- Color: red
- Type: Single, Receptacle
- Duty: Heavy Duty
- Special Features: Back,Side Wire

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- cUL Standard: Yes
- cU Rus: No

- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

#### Dimensions

- Depth (U S): 1.093"
- Height U S: 3.28"
- Width U S: 1.32"

#### Technical Information

- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Single
- Grade Type: Hospital

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 

#### resources BROCHURE

 Commercial & Industrial ProductsPDF (3.52mb)

#### CUTSHEET

 Hospital Grade Heavy Duty Single Receptacles, SF702R1PDF (146.18kb)