

Q9ljExMiigLz48L2E+IDxhIGIkPSJjdGwwNV9NYWlUtmF2MV9jdGwwMV9ycHRSZXNpZGVudGhbfF9jdGwwNI9ycHRSZXNpZGVudGhbfFN1Ym1lbnVfY3RsMI



designed to be better.

[Search](#)

## TradeMaster Decorator Duplex Receptacle, White

885W

Sierraplex Receptacle in white with screw terminal and speedwire. It is made with high impact-resistant thermoplastic construction. It has ultrasonic welding of face to back body and long-term blade retention. 15amp 125volt.

[Submit Query](#)

Where to buy

[Submit Query](#)

0

[Email](#) [Print](#)



Representative image shown.

### AVAILABLE OPTIONS



TradeMaster Decorator Duplex Receptacle, Black



TradeMaster Decorator Duplex Receptacle, Ivory



TradeMaster Decorator Duplex Receptacle, Light Almond

- SPECIFICATIONS
- YOU MIGHT LIKE

### features & benefits

- Extra-long strap. Quickloop wire looping aid. Tri-drive screws. Extra-large circuit break-off tabs.
- Side-access push wire release. Side wire accepts #12 - #14 AWG solid. Push wire accepts #14 AWG solid only.
- Self-grounding models provide automatic ground clip.

### specifications

#### General Info

- Color: White
- Number Of Poles: 2
- Number Of Wires: 3

#### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No.42
- CSA Standard: Yes

- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121704

**Dimensions**

- Depth (U S): 1"
- Height U S: 3.31"
- Width U S: 1.29"

**Technical Information**

- Amps: 15
- Volts: 125
- Volts A C: 125

**Buy American Act Compliance**

- Country of Origin: CHINA
- Buy American Act Status: No
- 

**you might like**



**Plugmold Multi-Outlet Strips**  
[View Details](#)



**Metal Raceway**  
[View Details](#)



**CornerMate Cord Organizer**  
[View Details](#)