













Rotary Fan Speed Controls  94301		May be Ganged Without De-Rating	
		HANGABLE	SHELVABLE
 Individual Package 3.875" x 5.875" x 1.56"		 Individual Package 3.875" x 5.875" x 1.56"	 Cut Case 4" x 6" x 17"
		6 Individual Clams in Cut Case	
Ivory	3A Max, Dial 5A Max, 3-Way Preset, Push On/Off, RFI Protected 6A Max, Dial, Adjustable Trim, RFI Protected		94301IV 94503IV 94601IV
Light Almond	3A Max, Dial		94301LAV
White	3A Max, Dial 6A Max, Dial, Adjustable Trim, RFI Protected		94301WV 94601WV
Standard			
 		UPC Codes on Appendix p. UPC2	P&S Catalog Section M

1.5A Max, No-Noise, De-Hummer Rotary Fan Speed Controls  94004		RFI Protected	
		HANGABLE	SHELVABLE
 Individual Package 3.875" x 5.875" x 1.56"		 Individual Package 3.875" x 5.875" x 1.56"	 Cut Case 4" x 6" x 17"
		6 Individual Clams in Cut Case	
Clear	4-Speed, Low-High		94004CLV
Ivory	3-Speed, Low-Med-High 4-Speed, Low-High		94003IV 94004IV
Light Almond	3-Speed, Low-Med-High		94003LAV
White	3-Speed, Low-Med-High 4-Speed, Low-High		94003WV 94004WV
Standard			
 		UPC Codes on Appendix p. UPC2	P&S Catalog Section M