

mluZy1kZXZpY2VzL2ZsZXhjb3lt2lyZS1tZXNoLWdyaXBzLmFzcHgiPjxpbWcgcmVwbGFjZT0iZHNyYyYlgZHNyYz0iL34vbWVkaWEvRTg5ODdDNTQ0NjFDND



designed to be better.

Search

# Toggle Time Delay Switch, White

97352W

Timer 1-60min Double Pole/Double Throw 500w/3hp 120v, White

Submit Query

Where to buy Enter Postal Code

Submit Query

Like 0

Tweet 0

0

Email Print



## product gallery

Representative images shown.

## AVAILABLE OPTIONS







Toggle Time Delay Switch, Ivory

- SPECIFICATIONS
- RESOURCES

### features & benefits

- Eliminates the need for two switches.
- Fits standard toggle opening for easy ganging.
- Time range adjustable from 1-60 minutes.
- Easily installed.
- May control one or two loads simultaneously.
- Motor rated.
- Silent operation.
- Reliable solid-state construction.
- Energy saving.

### Top 5 Resources

-  [Sensors & Timers \(Brochure\)](#)
-  [Commercial Lighting Controls \(Brochure\)](#)

### specifications

#### General Info

- Color: White
- Type: Dual Toggle

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Standard: Yes
- U N SPS C: 39121559

#### Dimensions

- Depth (U S): 1.50"
- Height U S: 4.15"
- Width U S: 1.80"

#### Technical Information



- Volts: 120VAC
- Watts: 500

#### Buy American Act Compliance

- Country of Origin: CHINA
- Buy American Act Status: No
- 

### resources

#### BROCHURE

-  [Sensors & TimersPDF \(578.46kb\)](#)
-  [Commercial Lighting ControlsPDF \(323.03kb\)](#)