



designed to be better.

Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Ivory

CR15I

Commercial Spec Grade Duplex Receptacle, Side Wire 15amp 125volt, Ivory

Where to buy

Like



•



•



•



product gallery

Representative images shown.

AVAILABLE OPTIONS



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, White



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Brown



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Gray



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Light Almond

- SPECIFICATIONS
- RESOURCES

features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Top 5 Resources

 [Commercial Grade Receptacles, SF304R1 \(Cutsheet\)](#)

specifications

General Info

- Color: Ivory
- Type: Receptacles
- Special Features: Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.78"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Commercial

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources CUTSHEET

 Commercial Grade Receptacles, SF304R1PDF (448.78kb)