

F0ZXNkAgMPDxYCHwQFGy93YWxsLXBsYXRlcy9kZWNvcmF0b3luYXNweGQWAmYPFglfAAWBATxpbWcgcmVwbGFjZT0iZHNyYyIlgZHNyYz0iL34vbWVke



designed to be better.

Search

Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Light Almond

CR15LA

Commercial Spec Grade Duplex Receptacle, Side Wire 15amp 125volt, Light Almond

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, White



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Brown



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Gray



Commercial Spec Grade Receptacle, Side Wire, 15A, 125V, Ivory


- SPECIFICATIONS
- RESOURCES

features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- Accepts #14 - #10 AWG solid or stranded copper or copper-clad wire.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.

- Auto-ground clip assures positive ground.

Top 5 Resources

 [Commercial Grade Receptacles, SF304R1 \(Cutsheet\)](#)

specifications

General Info

- Color: light almond
- Type: Receptacles
- Special Features: Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Rus: No
- Federal Spec: No
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.78"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Commercial


Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

CUTSHEET

 [Commercial Grade Receptacles, SF304R1PDF \(448.78kb\)](#)