

YWJsZSBNYW5hZ2VtZW50PC9hPiA8dWwgY2xhc3M9ImhpZGUtbnV3Jj4gPGxpIGNsYXNzPSJjb2wylj4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N0bDAy



designed to be better.

Search

Corrosion-Resistant Connector

CR6364

Turnlok Connector 2pole 3wire 50amp 125/250volt Corrosion Resistant

Submit Query

Where to buy

Submit Query

0

Email Print



Representative image shown.

- SPECIFICATIONS
- RESOURCES

features & benefits

- Quality Materials, durability, and time-tested design

Top 5 Resources

- Commercial & Industrial Products (Brochure)
- Plugs & Connectors (Brochure)

specifications

General Info

- Type: Connector
- Number Of Wires: 4
- Special Features: Corrosion-Resistant

Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

Dimensions

- Diameter U S: 2.26"
- Length: 3.90"

Technical Information



- Amps: 50 Amp
- Volts: 125/250V
- Volts A C: 125/250

Buy American Act Compliance

- Country of Origin: UNITED STATES OF AMERICA
- Buy American Act Status: Buy American Act Compliant



RESOURCES
BROCHURE

-  Commercial & Industrial ProductsPDF (3.52mb)
-  Plugs & ConnectorsPDF (1.93mb)