

4vb25xL2xpZ2h0aW5nLWNvbnRyb2wtc3lzdGVtcy9yZmxjL21hc3Rlci1jb250cm9scy9sYzYwMDEuYXNweGQWAmYYPFglAAUeUkZMQyBFdmVudCBDb250cn



designed to be better.

Search

Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Ivory

CRB5262I

Construction Spec Grade Duplex Receptacle Back & Side Wire 15amp 125volt Ivory

Submit Query

Where to buy

Enter Postal Code

Submit Query

0

Email Print



Representative image shown.

AVAILABLE OPTIONS



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, White



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Brown



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Black



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Gray



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Light Almond



Construction Spec Grade Receptacles, Back & Side Wire, 15A, 125V, Red

- SPECIFICATIONS
- RESOURCES

features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

Top 5 Resources

- [Construction Grade Receptacles, SF303R1 \(Cutsheet\)](#)

specifications

General Info

- Color: Ivory
- Type: Receptacles
- Special Features: Back, Side Wire

Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

Dimensions

- Depth (U S): 0.78"
- Height U S: 3.281"
- Width U S: 1.322"

Technical Information

- Amps: 15 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Construction

Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
-



resources

CUTSHEET

- [Construction Grade Receptacles, SF303R1PDF \(427.8kb\)](#)