

1jb250cm9scy5hc3B4lj5MaWdodGluZyBDb250cm9sczwwYT4gPGRpdjBjbGFzc0Zm91cnRoLWx2bCBjb2wzlj4gPGEgaWQ9ImN0bDA1X01haW50YXYxX2N



designed to be better.

Search

# Construction Spec Grade Receptacles, Back & Side Wire, 20A, 125V, Ivory

CRB5362I

Construction Spec Grade Duplex Receptacle, Back & Side Wire, 20amp 125volt, Ivory

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS
- RESOURCES

## features & benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face and thermoplastic back body.
- 8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.
- Terminal compartments isolated from each other for positive conductor containment.
- Tri-drive terminal and mounting screws.
- Auto-ground clip assures positive ground.

## Top 5 Resources

- Construction Grade Receptacles, SF303R1 (Cutsheet)

## specifications

### General Info

- Color: Ivory
- Type: Receptacles
- Special Features: Back, Side Wire

### Listing Agencies/Third Party Information

- CSA Listing Info: C22.2 No. 42
- CSA Standard: Yes
- cU Rus: No
- Federal Spec: Yes
- Fed Spec Number: WC596
- UL Listing No: UL498
- UL Standard: Yes
- U N SPS C: 39121406
- U R: No

### Dimensions

- Depth (U S): 0.78"
- Height U S: 3.281"
- Width U S: 1.322"

### Technical Information


- Amps: 20 Amp
- Volts: 125V
- Volts A C: 125
- Capacity: Duplex
- Grade Type: Construction

**Buy American Act Compliance**

- Country of Origin: MEXICO
- Buy American Act Status: Trade Agreement Act Compliant
- 



**resources**  
**CUTSHEET**

 [Construction Grade Receptacles, SF303R1PDF \(427.8kb\)](#)