

AxX2hsTmV3TGluyalgaHJIZj0iL3dpcmVtb2xkL3dvcmtc3VyZmFjZS93b3JrLXN1cmZhY2UtbW9kdWxhci1wb3dlci5hc3B4Ij5Xb3JrIFN1cmZhY2UgTW9kdWxhc



designed to be better.

Search

## California Standard Flanged Inlet

CS6375

3pole 4wire 125/250volt Inlet

Submit Query

Where to buy

Submit Query

0



Representative image shown.

- SPECIFICATIONS

### features & benefits

- Quality Materials, durability, and time-tested design

### specifications

#### General Info

- Type: Flanged Inlet
- Number Of Wires: 4
- Special Features: California Standard

#### Listing Agencies/Third Party Information

- CSA Standard: Yes
- UL Listing No: 498
- UL Standard: Yes
- U N SPS C: 39121403

#### Dimensions

- Diameter U S: 3.50"

#### Technical Information

- Amps: 50 Amp
- Volts: 125/250V
- Volts A C: 125/250

#### Buy American Act Compliance

- Country of Origin: MEXICO
- Buy American Act Status: Buy American Act Compliant

